PV Oven Series

The **Covesion PV Oven Series** is specially designed to provide secure mounting and robust thermal stability for our PPLN crystals.



Key Features

- Compact and simple to use
- Fully insulated construction using a high performance plastic material
 - Low external temperature
 - Minimal air currents
- Auto-locating dowel pins allow crystals to be exchanged with minimal realignment.
- High temperature stability of ±0.01°C when used with OC1 Temperature Controller
- Various mounting options available, compatible with a range of opto-mechanical systems

Covesion's team of optical engineers have designed a range of PPLN crystal clips, ovens, temperature controllers and mounting accessories, providing a **complete PPLN system** for easy integration into your optical arrangement.

Our PPLN clips are easily mounted into the oven using the auto-locating pins. These also allow the PPLN clips to be swapped in and out with minimal realignment of the optical train.

Finely sprung pins in the oven lid hold the PPLN crystal clip securely in place. The oven and PPLN crystal can then be mounted in any orientation, flexible to your choice of optical arrangement.

Covesion recommends the **OC1 temperature controller** for high thermal stability of ± 0.01 °C. This long term stability can be maintained at any temperature between near-ambient and 200°C.



Product Code	Crystal Length (Max Suitable) mm	Oven Length, L mm	Recommended Products			
			PPLN Clip Kit	Mounting Adapters	Temperature Controller	
PV10	10	22	PC10	PVP1 ⁺ , PVP1R ⁺	*	
PV20	20	32	PC20	PVP2 ⁺ , PVP2R ⁺	OC1 * High stability (±0.01°C) temperature controller	
PV40	40	52	PC40	PVP2 ⁺ , PVP2R ⁺		

* For customers who have previously purchased ovens with a 6-pin plug, we offer an adapter lead for use with the OC1.

[†] Post-mounting adapter plate with standard M4 thread.

[‡] Flexure stage adapter.

tel: +44 (0)1794 521 638 fax: +44 (0)8709 289 714



PV Oven Series

version 1.1/2011





 $\overset{\circ}{\odot} \overset{\circ}{\odot}$

o

MEN





Detailed drawings available. Please contact Covesion for more information.

Pin Configuration			
1	Heater		
2	Oven detect		
3	Sensor		
4	N/C		
5	Oven detect		
6	N/C		
7	Heater		
8	Sensor		
7	Heater		

Cable plug type:	Lumberg SV80
Cable length:	~1.2m
Temperature sensor:	PT100
Heating method:	Resistive heater

Specifications			
Maximum crystal thickness ¹	1.0mm		
Temperature stability ²	±0.01°C		
Maximum operating temperature (continous)	210°C		
Optical height ³	18mm		
Aperture slot size (W x H)	7 x 2.5mm		
Operating voltage (power)	12V (3.6W) 18V (8.3W) 24V (15W)		



1. When used with PC clip kit, including 1mm thick ITO-coated glass.

2. When used with the OC1 controller from 5°C above ambient to 200°C.

3. Assuming a 0.5mm PPLN crystal and measured from screw-mounted base to aperture centre.

Accessories available: PC clip kits, mounting adapters, OC1 temperature controller and adapter leads.

For more information, please contact us at:

tel:	+44 (0)1794 521 638
fax:	+44 (0)8709 289 714

email: sales@covesion.com

www.covesion.com

Covesion Ltd. Unit A7, The Premier Centre, Premier Way, Romsey, SO51 9DG, UK Registered in England No. 06338847, VAT No. 943 1896 00 Copyright © 2010-2011 Covesion Ltd.